

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3925-20

Dome Glass CTC

Two-light flush mount with dome shaped alabaster glass, solid trim and decorative knobs. Center lock-up with matching finial. Antique Bronze finish.

- Antique Bronze finish.
- Alabaster Glass.
- Decorative details.

Category: Close-to-Ceiling

Finish: Antique Bronze (painted)

Construction: Steel Construction

Glass/Shade: Alabaster glass bowl



Diameter: 13-1/4"
Height: 5-7/8"

Glass
Width: 9-13/16"
Height: 3-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" octagonal recessed outlet box 13.1875" W., 1.375" ht., 13.1875" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Two 75w max. Medium Base E26 base ceramic sockets	cCSAus Damp location listed 1 year warranty