

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3951-09

Joy

Gleeful simplicity defines the Joy Collection. Refreshing and fashionable, arcing forms of metal and fluted glass shades are enhanced by a classic Brushed Nickel finish. This three-light inverted pendant with a truly transitional style is ideal for a variety of interior spaces, including kitchens, dining areas and living rooms.

Category: Pendants

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched glass bowl



Diameter: 19-1/2"
Height: 24-3/4"
Overall ht. w/stem: 113-3/4"

Glass: 19-1/2" dia.
Height: 6-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain or stem mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Two 6" lengths of stem included Canopy covers a standard 4" hexagonal recessed outlet box	Pre-wired 12 feet of wire supplied 120V	Quantity: 3 100W Medium Base Medium ceramic sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Chandelier, Hall and Foyer, Pendant, Wall bracket, fixtures are available