

DATE:

NAME:

PROJECT:

Incandescent

P400003-020

TYPE:

## Looking Glass

Whether for a mountain cabin or an urban retreat, the rustic charm of the Looking Glass collection is an artful display for romantic vintage lighting. Inspired by a timber frame farmhouse, its frame features iron elements that support clear, seeded glass reflectors. Hints of brass accentuate the mechanical details to enhance a vintage feel.

- Reminiscent of a timber frame farmhouse, the frame features iron elements that support clear, seeded glass reflectors.
- Hints of brass can be found on the mechanical details to enhance a vintage feel
- Ideal for a mountain cabin or an urban retreat.
- Antique Bronze finish with Natural Brass accents.
- Part of the Design Series Collections offering high style and design.

## Category: Chandeliers

Finish: Antique Bronze (painted)

Construction: Steel Construction

Glass/Shade: Clear Seeded glass diffuser



Diameter: 36-3/4" Length: 19" Height: 18-1/4" Overall Ht. W/Stem: 84"

Glass Width: 7-7/8" Height: 1-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem mounted	Pre-wired	Quantity:	cULus Dry location listed
Mounting strap for outlet box included Two pieces of six links of 9 gauge chain supplied Two 6", eight 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 15.75" W., 0.8125" ht., 4.75" depth	15 feet of wire supplied 120 V	Six 60w max. Medium Base E26 base socket	1 year warranty