

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400015-009

Debut

A new category of vintage modern fixtures takes center stage with this six-light chandelier from one of our Design Series collections. Delicate details in a Brushed Nickel finish, create statement making focal pieces for a variety of interiors. Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades available in clear or frosted seeded finishes.

- Brushed Nickel finish
- A uniquely vintage modern feel
- Delicate details with a warm finish
- Makes a great statement piece for a variety of interiors
- Glass accessory shades in clear (P860003-001) or frosted (P860002-001) seeded finishes are available

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel construction



Diameter: 28"

Height: 27-1/2"

Overall Ht. W/Chain: 102-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box 5.6875" W., 1.4375" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Six 60w max. Medium Base E26 base ceramic socket	cULus Dry location listed 1 year warranty