

Project:			
Fixture Type:			
Location:			

Contact:

## P400047-143

## **Briarwood**

The Briarwood collection features a classic pattern commonly found on barn or farmhouse doors and gates. The simple geometric form features a faux-painted wood enclosure to frame vintage-style light bulbs. A coast-al-inspired whitewashed finish paired with Graphite details. Five-Light linear chandelier.

- Features a classic pattern commonly found on barn or farmhouse doors and gates
- Faux-painted wood-look enclosure to frame vintage-style light bulbs.
- · Coastal-inspired whitewashed finish paired with Graphite details.

Category: Chandeliers
Finish: Graphite (painted)
Construction: Steel Construction



Square: 20 in Height: 12 in

Overall Ht. W/Stem: 88 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Four 100 W max. Medium Base or	CULus Dry Location Listed
Mounting strap for outlet box included	15 feet of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base socket	
Six links of 9 gauge chain supplied	<del></del>		
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 6" W., 1" ht., 6" depth			