

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400048-031 Briarwood

Briarwood Collection 5-Light Matte Black Farmhouse Linear Island Chandelier Light

Category: Chandeliers
Finish: Textured Black (Painted)
Construction: Steel Construction



Length: 38 in
Depth: 10 in
Height: 9 in
Overall Ht. W/Chain And Stem: 75 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	15 feet of wire supplied	Quantity: five 100 W max.	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
six links of 9 gauge chain supplied			
one 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 16" W., 0.813" ht., 4" depth			