

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400051-143

Remix

Adding to the eclectic and nostalgic feel of the Remix collections, this funky chandelier is a traditional complement to many styles. Overscale tubular arms support a contrasting socket and bobèche for the perfect perch to display elegant vintage light bulbs. The style lends itself to be used with a wide range of home decor styles, including farmhouse and, industrial and many others.

- Industrial inspired design.
- Simple lines and curved arms
- Brushed Nickel accents.
- Graphite finish.
- Part of the Design Series Collections offering high style and design.

Category: Chandeliers

Finish: Graphite (painted)

Construction: Steel Construction



Diameter: 26"
Height: 20"
Overall Ht. W/Stem: 86"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.75" ht., 5" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Five 60w max. Medium Base E26 base socket	cULus Dry location listed 1 year warranty