

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400055-020

Barnes Mill

Rustic and vintage decor can transform your home into a nostalgic retreat reminiscent of rural farmhouses. Exposed iron details and a faux-painted wooden plank support artful, clear, seeded glass shades. Combine with vintage-style light bulbs to create a romantic focal point for any room. One-Light mini-pendant.

- Rustic and vintage lighting that transforms a home into a nostalgic retreat.
- A faux-painted wooden plank support artful clear, seeded glass shades
- Design reminiscent of rural farmhouses
- Exposed iron details.
- Antique Bronze finish.
- Combine with vintage-style light bulbs to create a romantic focal point to any room.

Category: Island/Linear

Finish: Antique Bronze (painted)

Construction: Steel Construction

Glass/Shade: Clear Seeded glass shades



Width: 38"
Height: 22-5/8"
Depth: 4"
Overall Ht. W/Chain: 96-1/2"

Glass
Width: 6-5/16"
Height: 3.-15/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Two pieces of six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 7.875" W., 0.8125" ht., 4.5" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Five 100w max. Medium Base E26 base socket	cULus Dry location listed 1 year warranty