

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P400066-015

## Tinsley

Featuring soft angles and impressive sculptural curves, Tinsley is a refreshingly updated design for Luxe, Transitional and Traditional interiors. The frame is complemented by classic etched glass shades or open candle designs. Overscaled details found in Tinsley are ideal for welcoming guests and visitors in a foyer or entryway, as well as in luxe dining room or traditional living room settings.



**Diameter: 23"**  
**Height: 24"**  
**Overall Ht. W/Chain: 99"**

- Overscaled details found in Tinsley are ideal for welcoming guests and visitors in a foyer or entryway, as well as in luxe dining room or traditional living room settings
- Features soft angles and impressive sculptural curves
- Popular Polished Chrome finish
- Frame is complemented by classic etched glass shades or open candle designs
- Uses five 60-watt max. candelabra style bulbs (sold separately)
- Tinsley is a refreshingly updated design for Luxe, Transitional and Traditional interiors
- Chandeliers have the ability to change the look of a room – try over a dining room table, in a bath and vanity setting or other spaces that are in need of ambient illumination and decorative décor

**Category:** Chandeliers

**Finish:** Polished Chrome (plated)

**Construction:** Steel construction

**Glass/Shade:** Etched Glass

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Hanging mounted  Mounting strap for outlet box included  Six feet of 9 gauge chain supplied  Canopy covers a standard 4" octagonal recessed outlet box  5.5" W., 1" ht., 5.5" depth	15 feet of wire supplied  120 V	Quantity:  Five 60w max. candelabra  E12 base	cULus Dry location listed  1 year limited warranty