

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P400081-020

## Fontayne

With updated designs that honor the charm of early American styling, Fontayne six-light chandelier provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces. Impressive graphic elements take center stage, while candelabra lights highlight subtle curves. Dual tone finish combinations of Antique Bronze with faux oak accents.

- Features updated designs that honor the charm of early American styling
- Dramatic circular frame offers a stylish perch for graceful candelabra lights
- Dual tone finish combination is Antique Bronze with hand painted weather oak accents
- Uses six 60 watt max. candelabra base lamps
- Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces
- Ideal for welcoming guests and visitors in a foyer or entryway, as well as in dining room or traditional living room settings
- Progress Lighting Design Series, a collection offering fashionable styles and affordable luxury.

**Category:** Chandeliers

**Finish:** Antique Bronze (painted)

**Construction:** Steel Construction



**Diameter:** 22"

**Height:** 36-5/16"

**Overall Ht. W/Chain:** 111-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Hanging mounted  Mounting strap for outlet box included  Six feet of 9 gauge chain supplied  Canopy covers a standard 4" octagonal recessed outlet box  5.125" W., 0.75" ht., 5.125" depth	15 feet of wire supplied  120 V	Quantity:  Six 60w max. Candelabra Base  E12 base	cETLus Dry location listed  1 year limited warranty