## **PROGRESS** LIGHTING<sup>™</sup>

Project: Fixture Type:

Location:

Contact:

## P400095-009 Kene

Add a modern romance to the heart of your home with this lovely chandelier. Quiet etched glass diffusers are surrounded by clear outer glass shades for a soft, luxurious touch. The shades sit on an elegant brushed nickel frame with gently flowing arms.

- Quiet etched glass diffusers are surrounded by clear outer glass shades for a soft, luxurious touch.
- The shades sit on an elegant brushed nickel frame with gently flowing arms.
- Add a modern romance to the heart of your home with this lovely chandelier.
- · Ideal for any foyer, kitchen, or dining room.
- Perfect for modern, Craftsman, or contemporary settings.
- Measures 27-1/4-inch width by 22-1/2-inch height.
- Uses five medium base bulbs that is sold separately (100w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade, Etched Glass Cylindrical Shade



Diameter: 27-1/4 in Height: 22-1/2 in Overall Ht. W/Chain: 97-1/2 in

Clear glass Cylindrical Shade Width: 4-3/4 in Height: 5-9/16 in

Etched Glass Cylindrical Shade Width: 2-15/16 in Height: 4-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Five 75 W max. Medium Base or	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain sockets	
6 feet of 9 gauge chain supplied			

Canopy covers a standard 4" recessed outlet box: 5.125" W., 1.1875" ht., 5.125" depth