

Project:		
Fixture Type:		
Location:		
Contact:		

P400096-143

Kene

Add a modern romance to the heart of your home with this lovely chandelier. Quiet etched glass diffusers are surrounded by clear outer glass shades for a soft, luxurious touch. The shades sit on an elegant graphite frame with gently flowing arms.

- Quiet etched glass diffusers are surrounded by clear outer glass shades for a soft, luxurious touch.
- The shades sit on an elegant graphite frame with gently flowing arms.
- $\boldsymbol{\cdot}$ Add a modern romance to the heart of your home with this lovely chandelier.
- · Ideal for any foyer, kitchen, or dining room.
- · Perfect for modern, Craftsman, or contemporary settings.
- · Measures 32-3/4-inch width by 29-7/8-inch height.
- Uses nine medium base bulbs that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers
Finish: Graphite (Painted)
Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade, Etched Glass Cylindrical Shade



Diameter: 32-3/4 in Height: 29-7/8 in

Overall Ht. W/Chain: 152-1/2 in

Clear glass Cylindrical Shade

Width: 4-3/4 in Height: 5-9/16 in

Etched Glass Cylindrical Shade

Width: 2-15/16 in Height: 4-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Nine 75 W max. Medium Base or	CULus Dry Location Listed
1/4 IP mounting plate for outlet box included	15 feet of wire supplied	LED equivalent	1-year Limited Warranty
10 feet of 9 gauge chain supplied	120 V	E26 base Porcelain sockets	
Canopy covers a standard 4" recessed outlet box: 5.125" W., 1.1875" ht., 5.125" depth			