

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P400097-143

Gulliver

Three circular bands wrap together to create an open design for Gulliver four-light linear chandelier. Dual toned frame color combinations of Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.

- Design complements Rustic and Modern Farmhouse home decor accents, as well as Urban Industrial and Coastal interior settings
- Metal banding features embossed wood grain pattern for rich visual texture
- Hand painted Graphite finish with weathered gray accents
- Dual toned frame emulates popular design style that contains mixed metal accents
- Island fixture uses four 75W max. medium base lamps including LED equivalent
- Shop the complete Gulliver collection for a coordinated look throughout your entire home or mix and match with other complementary styles for a more curated decor
- Can be used over kitchen islands, in a breakfast nook or over dining room tables.

Category: Chandeliers
Finish: Graphite (painted)
Construction: Steel Construction



Width: 38-1/2" Height: 17" Depth: 10-1/2"

Overall Ht. W/Chain: 91-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Hanging mounted	15 feet of wire supplied	Quantity:	cETLus Dry location listed
Mounting strap for outlet box included	120 V	Four 75w max. Medium Base E26 base	1 year limited warranty
Two pieces of six feet of 9 gauge chain supplied		220 8430	
Canopy covers a standard 4" octagonal recessed outlet box			
13.375" W., 0.5" ht., 4.75" depth			