

DATE:

NAME:

PROJECT:

Incandescent

## P400114-143

TYPE:

## Blakely

The Blakely collection six-light linear chandelier is a fashion-forward design styles. An open linear form celebrates geometric interplay with clean, straight lines. Finished in Graphite with satin brass accents, the Blakely collection is ideal for Modern and Traditional interiors.

- The open-form Blakely fixtures has Satin Brass candles on a sturdy iron frames—a fresh remake of traditional style
- This six-light island is ideal for dining rooms or long, casual breakfast areas
- Its fashion-forward style complements both Modern and Traditional interiors
- The frame's Graphite finish sets off the Satin Brass candle lamps
- Measures 40in L x 15 5/8in ht. x 15in W
- Uses six 60-watt max candelabra base bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

## Category: Chandeliers

Finish: Graphite (painted)

Construction: Steel Construction



Width: 40" Length: 40" Height: 15-5/8" Depth: 15" Overall Ht. W/Chain: 82"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Pre-wired	Quantity:	cULus Dry location listed
Mounting strap for outlet box included	15 feet of wire supplied	Six 60w max. Candelabra Base	1 year warranty
Two pieces of six links of 9 gauge chain supplied	120 V	E12 base phenolic sockets	
Two 6", eight 12" lengths of stem included			
Canopy covers a standard 4" octagonal recessed outlet box			
14" W., 0.75" ht., 4.5" depth			