

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P400115-104

### Seneca

The airy, open-cage design of the Seneca five-light chandelier makes it an excellent choice for providing a welcoming glow in an entryway or as they enjoy a meal at a dining table to kitchen island. Clean, Polished Nickel arms flow down from the orb crowning the fixture. Classic candelabra lights play along the fixture's smooth, round base, making it an elegant choice for modern farmhouse and luxe interiors.

- Perfect for providing class and light as guests are entertained at a dining table or kitchen island
- Five elegant candelabra lights appear to float in midair as they ornament the smooth frame
- The simple, sophisticated design is composed of clean lines that create generous, open space for the glowing candelabra lights
- Sleek, curved arms radiate outward from the simple orb crowning the refined fixture
- Finished in stunning Polished Nickel
- Clean, modern design is ideal for modern farmhouse and luxe interiors
- Uses five 60-watt max candelabra base bulbs, or the LED equivalents, that are sold separately
- Measures 25-1/2 in diameter X 15-7/8 in height, Overall height with stem 81-1/2 in, wire 180 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

**Category:** Chandeliers

**Finish:** Polished Nickel (Plated)

**Construction:** Steel Construction



Diameter: 25-1/2 in

Height: 15-7/8 in

Overall Ht. W/Chain And Stem: 81-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain mounted	Prewired	Quantity:	CULus Dry Location Listed
Mounting strap for outlet box included	15 feet of wire supplied	Five 60 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 4.75" W., 0.75" ht., 4.75" depth			