

DATE:

TYPE:

NAME:

PROJECT:

P400118-009

Clifton Heights

Distinctive chiseled features and clean lines are key features within the Clifton Heights collection. Inspired by an updated interpretation of Craftsman styling, careful attention to the details delivers a dramatic accent. A Brushed Nickel finish complements elegant etched square glass shades. The Clifton Heights collection enhances a variety of home styles including Farmhouse, Craftsman and Transitional decor. Four-Light Chandelier.

- Distinctive forms and clean lines are key features within the Clifton Heights collection
- Inspired by Craftsman styling, special attention to decorative details can be appreciated in each fixture
- Elegant etched glass shades
- Brushed Nickel finish
- 4-light chandelier ideal for dining rooms or breakfast nooks
- Uses 4, 100-watt max. medium base bulbs including LED equivalent (sold separately)
- Ideal for Farmhouse and Transitional spaces
- Measures 21" diameter x 23 1/2" H
- Overall length with chain 97 1/2"
- Dry location listed
- Shop the complete Clifton Heights collection for a coordinated look throughout your entire home or mix and match with other complementary styles for a more curated decor

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass/Shade: Etched Glass Shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain mounted	Pre-wired	Quantity:	cULus Dry location listed
Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 1.125" ht., 4.75" depth	15 feet of wire supplied 120 V	Four 100w max. Medium Base E26 base Porcelain sockets	1-year limited warranty



Diameter: 21" Height: 23-1/2" Overall Ht. W/Chain: 97-1/2"

Height: 6-1/2"