PROGRESS LIGHTING

Project:		
Fixture Type:		
Location:		

Contact:

P400119-31M Clifton Heights

Clifton Heights Collection Six-Light Modern Farmhouse Matte Black Etched Glass Chandelier Light

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Etched Glass Square/Rectangular



Diameter: 26 in Height: 23-1/2 in Overall Ht. W/Chain: 99-1/2 in

Etched Glass Square/Rectangular Width: 5-1/2 in Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(6) Medium Base (E26) Lamp Type A19	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Incandescent: 100-watt MAX per socket	1-year Limited Warranty
6 feet of 9 Gauge chain supplied		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 4.75" W., 1.12" ht., 4.75" depth		bulbs	