

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_


NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

# P400132-009

## Calhoun

A trend in home decor is the repurposing of antique pieces. The Calhoun Collection playfully follows this trend with an apothecary style clear glass diffuser held in place with a mechanical latch from a spice container. A glass shade showcases a thickened profile to create a vintage-style surface for a classic handmade appearance. The vintage design is a perfect complement to several decor styles including the popular Farmhouse trend. Calhoun is a versatile style that can be displayed in three different ways: assemble with the included optional spanner and long or short stems for a unique cord-hung style chandelier, or let the lights hang in a more casual cluster. Three-Light Chandelier with a Brushed Nickel finish.



**Diameter: 22-5/8"**  
**Height: 29-1/8"**  
**Overall Ht. W/Chain: 103"**

**Glass**  
**Height: 6-3/4"**

- Calhoun is a versatile collection that can be displayed in a variety of different ways for added customization in the home
- Uses 3, 60-watt max. medium base bulbs including LED equivalent (sold separately)
- Clear glass shades inspired by apothecary jars add a vintage feel to Calhoun's casual forms
- Assemble optional 3-pronged spanner to fit black cloth-covered cords in each arm - or let each cloth cord hang as a light grouping or cluster display
- Supplied with (1) 6" and (1) 12" stems and spanner to customize installation of fixture. Stems can also be used in conjunction with included chain for suspension from the ceiling
- Calhoun's versatile design ideal for Farmhouse, Coastal and Industrial settings
- Measures 22 5/8" diameter x 29 1/8" H (when installed with spanner)
- Can be displayed in living rooms, breakfast nooks, kitchens - and even paired in groupings of two or more over a dining room table

**Category:** Chandeliers

**Finish:** Brushed Nickel (plated)

**Construction:** Steel construction

**Glass/Shade:** Clear Glass Shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied One 6", one 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.75" ht., 5" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Three 60w max. Medium Base E26 base Porcelain sockets	cULus Dry location listed 1-year limited warranty