

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P400141-009

Nealy

The Nealy Collection five-light chandelier offers classic charm with an edge of modern luxury. Curving details are complemented by luxurious white silk shades. Featuring mixed metal influences, the Brushed Nickel frame is accentuated with Graphite straps and completed with K9 glass over brass-tone candle holders.

- Brass-infused glass accents punctuate the sinuous mixed-metal curves of Nealy's collection
- With our without the white silk shades, the five-light chandelier adds modern-luxury flair to your room
- Ideal for a formal living room, dining room or master bedroom
- With its jewelry-like styling, it's well-suited for Modern and Luxe interiors
- Classic Brushed Nickel Finish frame with Graphite detailing
- Measures 28 3/8in diameter x 28 1/4in height
- Uses five, 60-watt max. candelabra base bulbs or LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Chandeliers

Finish: Brushed Nickel (plated)
Construction: Steel Construction
Glass/Shade: White Silk Shades



Diameter: 28-3/8" Height: 28-1/4"

Overall Ht. W/Chain: 102-1/2"

Width: 5-1/2" Height: 5-5/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Pre-wired	Quantity:	cULus Dry location listed
Mounting center lock-up for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.75" ht., 5" depth	15 feet of wire supplied 120 V	Five 60w max. Candelabra Base E12 base phenolic sockets	1 year warranty