

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

# P400149-078

## Zag

Calming organic forms are the focal point in Zag's branching design . Inspired by European styling, the five-light Vintage Gold chandelier is ideal for Modern and Transitional interiors. The streamlined minimalist frame is the perfect showcase for globe or vintage style light bulbs.

- Calming organic forms are the focal point in Zag's whimsical design
- 5-light chandelier
- Uses 5, 60-watt max. medium base bulbs including LED equivalent (sold separately)
- Finished in Vintage Gold finish
- Zag's natural flowing features are a perfect showcase for vintage lamps or globe style light bulbs
- Measures 18" diameter x 21 5/8" H (without bulbs)
- Overall length with stem is 78"
- Convertible to semi-flush
- Inspired by European styling, these chandelier options are ideal for Mid Century and Modern interiors
- Dry location listed

**Category:** Chandeliers

**Finish:** Vintage Gold (painted)

**Construction:** Steel construction



**Diameter: 18"**  
**Height: 21-5/8"**  
**Overall Ht. W/Stem: 78"**

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung mounted Mounting plate for outlet box included One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.875" W., 0.875" ht., 4.875" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Five 60w max. Medium BaseE26 base Porcelain sockets	cULus Dry location listed 1-year limited warranty