

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P400153-071

Foster

The airy, antique frame of the Foster five-light chandelier allows exposed, vintage bulbs to shine light upon the memories being made below at a dining table or kitchen island. The squared lines, rounded metal arms, and mixed metal elements draw inspiration from the industrial and rustic settings for which it is perfect for illuminating.

- Ideal for installing over a library table, in an office, den, or wherever a touch of antique detailing is desired
- Squared lines and mixed metal elements are ideal for industrial and rustic settings
- Five-light chandelier with rounded, iron metal arms holding the bulbs in an open, circular design
- Exposed bulbs held by decorative sockets perch on the circular center frame, adding a vintage charm
- Gilded Iron finish complements the fixture's clean ironwork styling
- Ironwork design rooted in antique-inspiration
- Measures 25 in diameter X 14 in height, Overall height with stem 80-1/2 in, wire 180 in
- Uses five 60-watt max medium base bulbs, or the LED equivalents, that are sold separately
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Chandeliers

Finish: Gilded Iron (Painted)

Construction: Steel Construction



Diameter: 25"
Height: 14"
Overall Ht. W/Chain And Stem: 80-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain mounted Mounting Plate for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 5.125" ht., 0.875" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Five 60w max. Medium Base E26 base Porcelain sockets	cETLus Dry location listed