## **PROGRESS** LIGHTING<sup>™</sup>

roject:	
ixture Type:	
ocation:	

Contact:

## P400167-143 Rainey

Rainey Collection Five-Light Graphite Clear Fluted Ribbed Glass Modern Chandelier Light

Category: Chandeliers Finish: Graphite (Painted) Construction: Steel Construction Glass/Shade: Clear Fluted Ribbed Glass Shade

canopy covers a standard 4" recessed outlet box: 5.125" W., 0.875" ht., 5.125" depth



Diameter: 24 in Height: 22-1/4 in Overall Ht. W/Chain And Stem: 88-1/2 in

Clear Fluted Ribbed Glass Shade Width: 1-15/16 in Height: 7-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	Prewired	(5) Candelabra Base (E12) sockets	cULus Dry Location Listed
	15 feet of wire supplied		1-year Limited Warranty
Mounting strap for outlet box		Lamp Type B	5
included	120 V		
		Incandescent: 60-watt MAX per	
six links of 9 gauge chain		socket	
supplied (1)		LED: 12.5-watt MAX per socket	
one 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs.	