

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400168-143

Rainey

The Rainey Collection six-light chandelier embraces an artful display of asymmetrical design styling. A slender, staggered frame representing organic forms draws the eye upward to admire the clear fluted ribbed glass shades. The larger scale is suitable for open floor plans, great rooms or anywhere a dramatic focal piece is needed to make a bold statement. The Graphite finish is paired with Brushed Bronze accents.

- A modern study in asymmetrical design, the Rainey features a staggered frame that represents abstracted organic forms
- The six-light chandelier features fluted, ribbed glass shades
- The larger scale makes a bold focal point in great rooms, dining rooms and open-plan layouts
- Its contemporary sophistication is a natural choice for Modern, Mid-Century and Luxe interiors
- Graphite finish with brushed bronze accents
- Measures 28in diameter x 25 1/4in ht.
- Uses 6, 60-watt max. candelabra base bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Chandeliers

Finish: Graphite (plated)

Construction: Steel Construction

Glass/Shade: Clear Fluted Ribbed glass Shades



Diameter: 28"
Height: 25-1/4"
Overall Ht. W/Chain: 91-1/2"

Width: 1-15/16"

Height: 7-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 1" ht., 5.125" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Six 60w max. Candelabra Base E12 base phenolic sockets	cULus Dry location listed 1 year warranty