

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400172-078

Rigsby

The use of mixed media highlights a variety of elegant details are featured in the Rigsby Collection's five-light chandelier. A hint of faux marble appears in the horizontal cross bars, while Vintage Gold and Chrome accents create a dual toned finish. Decorated white gloss hardback shades lined with burnished gold foil complete the fixture.

- A hint of faux marble appears with the chrome metal arms.
- Gold-lined white-gloss shades give this five-light chandelier a burnished glow from within
- The brass, chrome and Carrera-like finishes evoke high-end kitchen styling, an ideal complement to similar finishes in a kitchen, breakfast room or bathroom
- Its contemporary restraint and mixed metals make this fixture suitable for Modern and Luxe interiors
- Sensuous Vintage Gold finish with Polished Chrome accents
- Measures 32in diameter x 16 3/4in ht.
- Uses five 60-watt max. medium base bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available P400173-078



Diameter: 32"
Height: 16-3/4"
Overall Ht. W/Chain: 92"

Width: 8"
Height: 4-3/4"

Category: Chandeliers

Finish: Vintage Gold (painted)

Construction: Steel Construction

Glass/Shade: White with Brush Gold Linen paper Shades

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.75" ht., 5" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Five 60w max. Medium Base E26 base porcelain sockets	cULus Dry location listed 1 year warranty