

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P400175-031

Seneca

Entertain guests at a dining table or kitchen island under the lavish glow of the Seneca six-light island chandelier. Smooth, sleek arms support six elegant candelabra lights as they gracefully stand shoulder to shoulder, gracefully exuding light on the memories being made below in any modern farmhouse or luxe setting.

- Perfect for providing class and light as you entertain guests at a dining table or kitchen island
- Six elegant candelabra lights stand shoulder to shoulder as they ornament the smooth frame
- The simple, sophisticated design is composed of clean lines that create generous open space for the glowing candelabra lights
- Sleek, curved arms radiate outward from the simple orb crowning the refined fixture
- Finished in bold Black and accented with painted antique nickel candelabra lights
- Clean, modern design is ideal for modern farmhouse and luxe interiors
- Uses six 60-watt max candelabra base bulbs, or the LED equivalents, that are sold separately
- Measures 38-1/4 in diameter X 14-1/8 in height Overall height with stem is 80-1/2 in, wire 180 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Island/Linear

Finish: Black (Painted)

Construction: Steel Construction



Width: 15-3/8"

Length: 38-1/4"

Height: 14-1/8"

Overall Ht. W/Chain And Stem: 80-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain mounted Mounting back plate for outlet box included Two pieces of six links of 9 gauge chain supplied Two 6", eight 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 14.375" W., 0.75" ht., 4.25" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Six 60w max. Candelabra Base E12 base Phenolic sockets	cULus Dry location listed