

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P400187-104

Seneca

Elegant candelabra lights dance in a beautiful, suspended ballet in the Seneca nine-light chandelier. Gorgeous, Polished Nickel arms radiate down from the orb crowning the fixture, creating an ethereal, open-cage design destined to exude a gracious glow over entryways, dining tables, and kitchen islands in modern farmhouse and luxe interiors.

- A must-have piece for romancing guests in an entryway or for inspiring conversation around a dining table or large kitchen island
- Nine elegant candelabra lights ornament the smooth frame
- The simple, sophisticated design is composed of clean lines that create generous, open space for glowing candelabra lights
- Sleek, curved arms radiate outward from the simple orb crowning the refined fixture
- Finished in stunning Polished Nickel
- Clean, modern, open-cage design is ideal for modern farmhouse and luxe interiors
- Uses nine 60-watt candelabra base bulbs, or the LED equivalents, that are sold separately
- Measures 30 in diameter X 20-7/8 in height, Overall height with the is 86-1/2 in, wire 180 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Chandeliers

Finish: Polished Nickel (Plated)

Construction: Steel Construction



Diameter: 30"

Height: 20-7/8"

Overall Ht. W/Chain And Stem: 86-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain mounted Mounting Strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 0.75" ht., 4.75" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Nine 60w max. Candelabra Base E12 base Phenolic sockets	cULus Dry location listed