

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P400192-160

Point Dume™ - Wandermere

With elegant out-stretched arms and the grace of a Calder mobile, the Wandermere chandelier is "modern symmetry in balance." Available in Brushed Brass with curved metal shades, the Wandermere is an architectural presence for any space. This fixture is part of Jeffrey Alan Marks Point DumeTM lighting collection which celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences.



Diameter: 40" Height: 28-1/4"

Overall Ht. W/Chain: 103-1/2"

Category: Chandeliers
Finish: Brushed Brass (plated)
Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Pre-wired	Quantity:	cETLus Dry location listed
Mounting strap for outlet box included Six feet of 9 gauge chain	15 feet of wire supplied 120 V	Eight 60w max. Candelabra Base E12 base Porcelain sockets	1 year warranty
supplied Canopy covers a standard 4" octagonal recessed outlet box			
6.75" W., 1.375" ht., 6.75" depth			