

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400194-031 Bowman

Beautiful lighting will appeal to both your classic taste and your artistic spirit with this chandelier. Wandering eyes will focus on clear, chiseled glass shades as they offer an air of refinery. Handsome light bases with dainty, sophisticated curved arms support elegant light bases. The frame is coated in a classic black finish to complete the versatile, eye-catching design.

- Wandering eyes will focus on clear, chiseled glass shades as they offer an air of refinery.
- The frame is coated in a classic black finish to complete the versatile, eye-catching design.
- Handsome light bases with dainty, sophisticated curved arms support elegant light bases.
- Ideal for any dining room, kitchen, or foyer.
- Perfect for transitional, rustic, farmhouse, or coastal settings.
- Measures 26-inch width by 23-1/4-inch height.
- Uses five candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Clear Chiseled glass bell shaped shade



Diameter: 26 in
Height: 23-1/4 in
Overall Ht. W/Chain: 98-1/4 in

Clear Chiseled glass bell shaped shade
Width: 4-13/16 in
Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	Five 60 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			