PROGRESS LIGHTING[™]

Project:	
Fixture Type:	
Location:	

Contact:

P400195-031 Bowman

Beautiful lighting will appeal to both your classic taste and your artistic spirit with the Bowman Collection Six Light Black Chandelier. Wandering eyes will focus on the clear, chiseled glass shade that encircles four elegant light sources gathering quietly at the light fixture's center. Handsome, black light bases with sophisticated curved arms originate from a decorative black knob that embellishes the outer bottom of the textured glass shade.

- Wandering eyes will focus on the clear, chiseled glass shade that encircles the elegant light sources gathering quietly at the light fixture's center.
- From the bottom of the sleek center column, a light base appears to gracefully drip down and provide an extra touch of refined visual interest.
- Ideal for any foyer, dining room, or kitchen.

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Construction

- A sophisticated choice for luxury, modern, and transitional interiors.
- Measures 32-inch width by 28-7/8-inch height.
- Uses four candelabra base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.

Glass/Shade: Clear Chiseled glass bell shaped shade

· Progress Lighting products are designed for exceptional quality, reliability, and functionality.



Diameter: 32 in Height: 28-7/8 in Overall Ht. W/Chain: 104 in

Clear Chiseled glass bell shaped shade Width: 4-13/16 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Six 60 W max. Candelabra Base	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E12 base Phenolic sockets	

6 feet of 9 gauge chain supplied

Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth