## **PROGRESS** LIGHTING<sup>™</sup>

Project:			
Fixture Type:			
Location:			

Contact:

## **P400197-009** Lassiter

Manifest a swoon-worthy lighting experience with the stunning blend of the modern and traditional styles in this one-of-a-kind chandelier. Square tubing with clean, sharp angles is coated in a beautiful brushed nickel finish that demands your attention. Striking vintage light sockets boast their bold yet simple demeanor as they hold clear glass shades to complete this state-ment-making light fixture.

- Coated in a beautiful brushed nickel finish.
- Square tubing with clean, sharp angles.
- Striking vintage light sockets demand your attention.
- · Clear glass shades complete the blend of modern and traditional styles.
- Ideal for any foyer, kitchen, or dining room.
- Measures 26-inch width by 26-inch height.
- Perfect for modern, new traditional, or contemporary settings.
- Uses five medium base bulbs that are sold separately (60w max LED or incandescent).
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear glass Cylindrical Shade



Diameter: 26 in Height: 26 in Overall Ht. W/Chain: 101 in

Clear glass Cylindrical Shade Width: 4 in Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Five 60 W max. Medium Base or	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain sockets	
6 feet of 9 gauge chain supplied			

Canopy covers a standard 4" recessed outlet box: 5.5" W., 1.125" ht., 5.5" depth