

Project:		
Fixture Type:		
Location:		
Contact:		

P400199-009

Durrell

This versatile chandelier from the Durrell Collection will easily find a home in a variety of settings in need of generous illumination. Light bases reminiscent of vintage candlesticks are coated in a beautiful brushed nickel finish and appear to float around the structure on gently curving metal arms. A wooden column coated in a ceruse white finish stretches elegantly at the light fixture's center to attach the design to a linked metal chain.

- Light bases reminiscent of vintage candlesticks are coated in a beautiful brushed nickel finish.
- The light bases appear to float around the structure on gently curving metal arms.
- A wooden column coated in a ceruse white finish stretches elegantly at the light fixture's center to attach the design to a linked metal chain.
- · Ideal for any foyer, hallway, dining room, or kitchen.
- · Perfect for rustic, farmhouse, and coastal settings.
- Measures 26-1/2-inch width by 22-1/2-inch height.
- ${\boldsymbol \cdot}$ Uses five candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers
Finish: Brushed Nickel (Plated)
Construction: Steel Construction



Diameter: 26-1/2 in Height: 22-1/2 in

Overall Ht. W/Chain: 97-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Five 60 W max. Candelabra Base	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E12 base Phenolic sockets	
6 feet of 9 gauge chain supplied			
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			