

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400205-020

Austelle

Your home will exude comfort and sophistication with the graceful Austelle Collection Five-Light Antique Bronze Chandelier. A breathtaking mesh shade takes center stage as light sockets with curved arms coated in a handsome antique bronze finish peek from within the rustic mesh shade's embrace. Decorative wooden beads string down from the center column to add a pinch of chic flair.

- Breathtaking mesh shade takes center stage in this light fixture's perfect demeanor of rustic elegance.
- Light sockets with curved arms coated in a handsome antique bronze finish peek from within the rustic mesh shade's embrace.
- Decorative wooden beads string down from the center column to add a pinch of chic flair.
- Ideal for any foyer, dining room, or kitchen.
- A graceful choice for bohemian, coastal, modern, or transitional interiors.
- Measures 24-inch width by 20-inch height.
- Uses five candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Antique Bronze (Painted)

Construction: Steel Construction



Diameter: 24 in
Height: 20 in
Overall Ht. W/Chain: 96 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Five 60 W max. Candelabra Base or LED equivalent	CETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	E12 base Phenolic sockets	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V		
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.75" ht., 5.125" depth			