

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400206-031 Winslett

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this five-light chandelier. Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines coated in a beautiful black finish. Lightly seeded glass shades rest in shiny pedestal light bases that adds an unexpected, but welcomed dash of modern personality to this clean, traditional design.

- Lightly seeded glass shades rest in shiny pedestal light bases that add an unexpected, but welcomed dash of modern personality to this clean, traditional design.
- Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines coated in a beautiful black finish.
- Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this five-light chandelier.
- Ideal for any dining room, kitchen, or foyer.
- Perfect for transitional, rustic, farmhouse, or coastal settings.
- Measures 27-1/8-inch width by 21-1/8-inch height.
- Uses five medium base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Clear Seeded glass Cylindrical Shade,



Diameter: 27-1/8 in
Height: 21-1/8 in
Overall Ht. W/Chain: 95-1/2 in

Clear Seeded glass Cylindrical Shade
Width: 4-3/4 in
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	180" of wire supplied	Five 60 W max. Medium Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E26 base Porcelain sockets	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			