## **PROGRESS** LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:

## P400208-009 Winslett

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this chandelier. Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines coated in a gorgeous brushed nickel finish. Lightly seeded glass shades rest in shiny pedestal light bases that add an unexpected, but welcomed dash of modern personality to this clean, traditional design.

- Lightly seeded glass shades rest in shiny pedestal light bases that add an unexpected, but welcomed dash of modern personality to this clean, traditional design.
- Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines coated in a gorgeous brushed nickel finish.
- Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the chandelier's beautiful craftsmanship.
- $\boldsymbol{\cdot}$  Ideal for any dining room, kitchen, or foyer.
- $\cdot\,$  Perfect for transitional, rustic, farmhouse, or coastal settings.
- Measures 34-1/8-inch width by 31-5/8-inch height.
- Uses nine medium base bulbs that are sold separately (60w max LED or incandescent).
- $\cdot\,$  Able to be fully dimmable with dimmable bulbs.

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction

Includes installation instructions and mounting hardware.

Glass/Shade: Clear Seeded glass Cylindrical Shade,

• Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Diameter: 34-1/8 in Height: 31-5/8 in Overall Ht. W/Chain: 155 in

Clear Seeded glass Cylindrical Shade Width: 4-3/4 in Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CULus Dry Location Listed
1/4 IP mounting plate for outlet box included	180" of wire supplied	Nine 60 W max. Medium Base or LED equivalent	1-year Limited Warranty
10 feet of 9 gauge chain supplied	120 V	E26 base Porcelain sockets	

Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth