

Project:			
Fixture Type:			
Location:			
Contact:			

P400209-009 Riley

Incorporate a sleek simplicity and natural beauty with the Riley Collection's Five-Light Brushed Nickel Chandelier. Clear glass shades are ready to offer stunning, rejuvenating illumination. The shades rest on a gorgeous brushed nickel frame with polished chrome accents that manifests feelings of tranquility and serenity.

- · Clear glass shades are ready to offer stunning, rejuvenating illumination.
- The shades rest on a gorgeous brushed nickel frame with polished chrome accents that manifests feelings of tranquility and serenity.
- Incorporate a sleek simplicity and natural beauty with this chandelier.
- · Ideal for any dining room, kitchen, or foyer.
- · Perfect for new traditional or contemporary settings.
- Measures 24-inch width by 19-3/4-inch height.
- Uses five candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade



Diameter: 24 in Height: 19-3/4 in

Overall Ht. W/Chain: 85-1/2 in

Clear glass Cylindrical Shade

Width: 2-3/8 in Height: 6-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain	Prewired	Quantity: Five 60 W max. Candelabra Base	CULus Dry Location Listed
1/8 IP mounting plate for outlet	15 feet of wire supplied	or LED equivalent	1-year Limited Warranty
box included	120 V	E12 base Phenolic sockets	
Six links of 9 gauge chain supplied			
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 4.875" W., 0.75" ht., 4.875" depth			