

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400210-031 Riley

Incorporate a sleek simplicity and natural beauty with this chandelier. Clear glass shades are ready to offer stunning, rejuvenating illumination. The shades rest on a gorgeous dual-tone frame with a black finish accented by a brushed nickel trim that manifests feelings of tranquility and serenity.

- Clear glass shades are ready to offer stunning, rejuvenating illumination.
- The shades rest on a gorgeous black frame with brushed nickel accents that manifests feelings of tranquility and serenity.
- Incorporate a sleek simplicity and natural beauty with this chandelier.
- Ideal for any dining room, kitchen, or foyer.
- Perfect for new traditional or contemporary settings.
- Measures 30-inch width by 25-1/8-inch height.
- Uses nine candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade



Diameter: 30 in
Height: 25-1/8 in
Overall Ht. W/Chain: 91 in

Clear glass Cylindrical Shade
Width: 2-3/8 in
Height: 6-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain	Prewired	Quantity:	CULus Dry Location Listed
1/4 IP mounting plate for outlet box included	15 feet of wire supplied	Nine 60 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 4.875" W., 0.75" ht., 4.875" depth			