

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400213-031 Torres

Elevate your mountain modern home décor by incorporating ravishing rustic design in the heart of your home with this chandelier from the Torres Collection. Handcrafted spires reminiscent of rugged forest surroundings coalesce in a cultivated masterpiece of rustic sophistication. Beautiful black, hammered edges crisscross in an open-cage design for an organic interpretation of the popular tic-tac-toe pattern.

- Handcrafted spires reminiscent of rugged forest surroundings coalesce in a cultivated masterpiece of rustic sophistication.
- Beautiful black, hammered edges crisscross in an open-cage design for an organic interpretation of the popular tic-tac-toe pattern.
- Elevate your mountain modern home décor by incorporating ravishing rustic design in the heart of your home with this chandelier.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for any modern, rustic, or bohemian settings.
- Measures 18-inch width by 11.62-inch height.
- Uses four candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Textured Black (Painted)

Construction: Steel Construction



Diameter: 18 in
Height: 11-5/8 in
Overall Ht. W/Chain: 77-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted	Prewired	Quantity: Four 60 W max. Candelabra Base or LED equivalent	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	E12 base Phenolic sockets	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V		
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			