

Project:			
Fixture Type:			
Location:			
Contact:			

## P400218-009

## **Durrell**

This versatile chandelier from the Durrell Collection will easily find a home in a variety of settings in need of generous illumination. A sailcloth linen shade creates a soft, muted glow. Inside the shade nestle light bases on gently curved arms coated in a beautiful brushed nickel finish. A wooden stem coated in a ceruse white finish attaches the light fixture to a linked chain.

- · Sailcloth linen shade creates a soft, muted glow.
- Inside the shade nestle light bases on gently curved arms coated in a beautiful brushed nickel finish.
- A wooden stem coated in a ceruse white finish attaches the light fixture to a linked chain.
- · Ideal for any foyer, hallway, dining room, or kitchen.
- $\boldsymbol{\cdot}$  Perfect for rustic, farmhouse, and coastal settings.
- Measures 21-inch width by 22-1/2-inch height.
- Uses four candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction

Glass/Shade: Sailcloth Linen Fabric drum shade



Diameter: 21 in Height: 22-1/2 in

Overall Ht. W/Chain: 97-1/2 in

Sailcloth Linen Fabric drum shade

Width: 21 in Height: 8-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Four 60 W max. Candelabra Base	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			