

Project:		
Fixture Type:		
Location:		
Contact:		

P400225-009

Chadwick

Stick with simple geometric forms and clean crisp lines with this modern wall bracket. Beautiful opal glass shades visually calm the sharp edges of the boxy frame in a masterful stroke of design excellence. The frame is coated in a classic brushed nickel finish that contrasts the light shades. The light fixture is just right for spaces in need of a subtle, feminine touch.

- Beautiful opal glass shades visually calm the sharp edges of the boxy frame in a masterful stroke of design excellence.
- The frame is coated in a classic brushed nickel finish that contrasts the light shades.
- The light fixture is just right for spaces in need of a subtle, feminine touch.
- · Ideal for any dining room or kitchen.
- · Perfect for transitional, modern, and contemporary settings.
- · Measures 40-inch width by 8-3/4-inch height.
- Uses three medium base bulbs that are sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction

Glass/Shade: Etched Opal glass Cylindrical Shade



Length: 40 inWidth: 40 in

Height: 8-3/4 in Depth: 12 in

Overall Ht. W/Stem: 59 in

Etched Opal glass Cylindrical Shade

Width: 4-5/16 in Height: 6-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Prewired	Quantity:	CULus Dry Location Listed
	15 feet of wire supplied	Three 100 W max. Medium Base or LED equivalent	1-year Limited Warranty
1/8 IP mounting plate for outlet box included	120 V	E26 base Porcelain sockets	
Two 6", eight 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 15.125" W., 0.75" ht., 4.5" depth			