

Project:

Fixture Type:

Location:

Contact:

P400250-031 Kellwyn

Kellwyn Collection 3-Light Matte Black Clear Glass Transitional Semi-Flush Mount Convertible Ceiling Light

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Length: 16 in Width: 16 in Height: 12-5/8 in

Overall Ht. W/Chain And Stem: 74-1/2 in

Clear Glass Cylindrical Width: 1-15/163 in

		Height: 7 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain/Semi-Flush	10 feet of wire supplied	Quantity: three 60 W max.	cULus Dry Location Listed
Mounting plate for outlet box included	120 V	E12 base Phenolic Socket	1-year Limited Warranty
48 in of 9 gauge chain supplied			
one 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.875" ht., 5.125" depth			