## **PROGRESS** LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:

## P400251-009 Kellwyn

Kellwyn Collection 5-Light Brushed Nickel Clear Glass Transitional Chandelier Light

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Length: 23 in Width: 23 in Height: 24-3/8 in Overall Ht. W/Chain And Stem: 75-1/2 in

Clear Glass Cylindrical Width: 1-15/163 in Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	Quantity: five 60 W max.	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 V	E12 base Phenolic Socket	1-year Limited Warranty
48 in of 9 gauge chain supplied			

one 12" lengths of stem included

Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.875" ht., 0.125" depth