

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400252-031 Kellwyn

Kellwyn Collection 9-Light Matte Black Clear Glass Transitional Chandelier Light

Category: Chandeliers
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Length: 28 in
Width: 28 in
Height: 34-1/4 in
Overall Ht. W/Chain And Stem: 109-1/2 in

Clear Glass Cylindrical
Width: 1-15/163 in
Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	Quantity: nine 60 W max.	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 V	E12 base Phenolic Socket	1-year Limited Warranty
6 feet of 9 gauge chain supplied			
one 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.875" ht., 5.125" depth			