

Project:			
Fixture Type:			
Location:			
Contact:			

P400253-009

Hedgerow

Hedgerow Collection 4-Light Grey Washed Oak Farmhouse Chandelier Light

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction



Length: 21-3/8 in Square: 21-3/8 in Height: 12-13/16 in

Overall Ht. W/Chain And Stem: 101-1/2 in

	overan in. Wy cham in the 1/2 m				
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION		
Ceiling/Stem + Chain	10 feet of wire supplied	Quantity: four 60 W max.	cULus Dry Location Listed		
1/8 IP mounting plate for outlet box included	120 V	E12 base Phenolic Socket	1-year Limited Warranty		
6 feet of 9 gauge chain supplied					
one 12" lengths of stem included					
Canopy covers a standard 4" recessed outlet box: 5.125" W., 1" ht., 5.125" depth					