

Project:			
Fixture Type:			
Location:			
C			

P400254-175

Hedgerow

 $\label{thm:condition} \mbox{Hedgerow Collection 5-Light Aged Oak Farmhouse Linear Island Chandelier Light}$

Category: Island/Linear

Finish: Distressed Brass (Painted) **Construction:** Steel Construction



Length: 40 in Depth: 11-3/8 in Height: 11 in

Overall Ht. W/Chain And Stem: 100-1/2 in

		Overall Tit. W/ chall Title Stell. 100 1/2 III			
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION		
Ceiling/Stem + Chain	15 feet of wire supplied	Quantity: five 60 W max.	cULus Dry Location Listed		
1/8 IP mounting plate for outlet box included	120 V	E12 base Phenolic Socket	1-year Limited Warranty		
6 feet of 9 gauge chain supplied					
two 12" lengths of stem included					
Canopy covers a standard 4" recessed outlet box: 12.187" W., 0.812" ht., 5.875" depth					