

Fixture Type:

Location:

Contact:

## Pivot LED

### Ceiling Stem Mounted • Damp Location Listed PROGRESS LED

### **Description:**

Pivot LED Collection Six-Light Satin White Modern Style Chandelier with Downlight

### **Specifications:**

- Frosted Acrylic Square/Rectangular
- Frosted Polycarbonate Round Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.125 in W., 1.375 in ht., 5.125 in depth
- + Mounting backplate for outlet box included
- 120 in of wire supplied

#### **Performance:**

| Number of Lights       | 6 + Downlight                      |
|------------------------|------------------------------------|
| Input Power            | 25 W                               |
| Input Voltage          | 120 V                              |
| Input Frequency        | 60 Hz                              |
| Lumens/LPW (Delivered) | 1,062/45 (LM-79)                   |
| CCT                    | 3000 K                             |
| CRI                    | 90 CRI                             |
| Life (hours)           | 50000 (L70/TM-21)                  |
| EMI/RFI                | FCC Title 47, Part 15, Class B     |
| Warranty               | 5-year Limited Warranty            |
| Labels                 | cETLus Damp Location Listed        |
|                        | Meets California Title 24 JA8-2019 |



#### **Dimensions:**

Diameter: 28-1/4 in Height: 8-3/4 in Overall Ht. W/Stem: 62-1/2 in

# P400260-028-30



## Pivot LED

Ceiling Stem Mounted • Damp Location Listed PROGRESS LED

### **Dimming Notes:**

P400260-028-30 is designed to be compatible with many ELV controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls:**

Lutron\_DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

# P400260-028-30