

Project:
Fixture Type:
Location:

Pivot LED

Ceiling Stem Mounted • Damp Location Listed PROGRESS LED

Contact:

Description:

Pivot LED Collection Modern Matte Black Chandelier with Downlight

Specifications:

- · Frosted Acrylic Square/Rectangular
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.125 in W., 1.375 in ht., 5.125 in depth
- · Mounting backplate for outlet box included
- 120 in of wire supplied

Performance:

Number of Lights	8 + Downlight
Input Power	29 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,303/45 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2019

P400261-031-30



Dimensions:

Diameter: 40 in Height: 10-1/16 in

Overall Ht. W/Stem: 63-7/8 in



Pivot LED

Ceiling Stem Mounted • Damp Location Listed PROGRESS LED

P400261-031-30

Dimming Notes:

 $\ensuremath{\mathsf{P400261\text{-}031\text{-}30}}$ is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.