

Ρ	ro	je	C	t:

Fixture Type:

Location:

Contact:

Kylo LED

Ceiling/Stem + Chain Mounted • Damp Location Listed PROGRESS LED

Description:

Kylo LED Collection 4-Light Matte Black Frosted Glass LED Modern Chandelier Light

Specifications:

- Frosted Acrylic Cylindrical
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.125 in W., 1.375 in ht., 5.125 in depth
- + Mounting backplate for outlet box included
- + 120 in of wire supplied 54 in

Performance:

Number of Modules	4	
Input Power	17 W	
Input Voltage	120 V	
Input Frequency	60 Hz	
Lumens/LPW (Delivered)	987/60 (LM-79)	
CCT	3000 K	
CRI	90 CRI	
Life (hours)	50000 (L70/TM-21)	
EMI/RFI	FCC Title 47, Part 15, Class B	
Warranty	5-year Limited Warranty	
Labels	cETLus Damp Location Listed	
	Meets California Title 24 JA8-2019	



Dimensions:

Length: 30 in Height: 21-1/4 in Overall Ht. W/Chain And Stem: 78-1/2 in

Frosted Acrylic Cylindrical Width: 1-1/4 in Height: 4-3/4 in



Kylo LED

Ceiling/Stem + Chain Mounted • Damp Location Listed PROGRESS LED

P400262-031-30

Dimming Notes:

P400262-031-30 is designed to be compatible with many ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.