

Project:

Fixture Type:

Location:

Contact:

Kylo LED

Ceiling/Stem + Chain Mounted • Damp Location Listed PROGRESS LED

Description:

Kylo LED Collection 6-Light Brushed Nickel Frosted Glass LED Modern Chandelier Light

Specifications:

- Frosted Acrylic Cylindrical
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.125 in W., 0.375 in ht., 5.125 in depth
- + Mounting backplate for outlet box included
- + 120 in of wire supplied 54 in

Performance:

Number of Modules	6
Input Power	25 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,505/65 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2019

P400263-009-30



Dimensions:

Length: 40 in Height: 22-3/4 in Overall Ht. W/Chain And Stem: 80 in

Frosted Acrylic Cylindrical Width: 1-1/4 in Height: 4-3/4 in



Kylo LED

Ceiling/Stem + Chain Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P400263-009-30 is designed to be compatible with many ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P400263-009-30