

Project:

Fixture Type:

Location:

Contact:

P400286-009

League

League Collection Five-Light Brushed Nickel and Etched Glass Modern Farmhouse Chandelier Light

Category: Chandeliers

Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical



Length: 24 in Diameter: 24 in Height: 18-5/8 in

Overall Ht. W/Chain: 70 in

Etched Glass Cylindrical

Width: 4-1/8 in Height: 5-1/2 in

	Height: 5-1/2 in		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	90 in of wire supplied	Quantity: five 100 W max. A19 or LED	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	equivalent	1-year Limited Warranty
		E26 base Porcelain Socket	
1 EA 48 in of 9 Gauge chain			
supplied with quick link		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4"			
recessed outlet box: 4.87" W., 0.81" ht., 4.87" depth			