



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400287-009 League

League Collection Four-Light Brushed Nickel and Etched Glass Modern Farmhouse Chandelier Light

Category: Island/Linear
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical



Length: 39-3/4 in
 Depth: 14 in
 Height: 14-1/2 in
 Overall Ht. W/Chain Or Stem: 77-1/2 in

Etched Glass Cylindrical
 Width: 4-1/8 in
 Height: 5-1/2 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---------------------------------------|---|--|
| Ceiling Chain 1/8 IP mounting plate for outlet box included Two pieces of 48 in of 9 Gauge chain supplied (2) with quick links two 12" lengths of stem included Canopy covers a standard 4" recessed outlet box: 1.37" W., 0.75" ht., 4.75" depth | 90 in of wire supplied 120 VAC | Quantity: four 100 W max. A19 or LED equivalent E26 base Porcelain Socket Fully dimmable with dimmable bulbs | cULus Dry Location Listed 1-year Limited Warranty |